

SIGMASCOPE® SMP350

Measuring the Electrical Conductivity of Nonferrous Metals



Measurement Principle, Applications and Hardware

Electrical conductivity is an important material property that provides information not only about a metal's ability to conduct electrical currents but also about its composition, micro-structure and/or mechanical properties. Using the SIGMASCOPE® SMP350, it is easy and quick to determine the electrical conductivity with precision and accuracy.

Measurement principle

The SIGMASCOPE® SMP350 measures the electrical conductivity according to the phase-sensitive eddy current method pursuant to DIN EN 2004-1 and ASTM E 1004. This kind of signal evaluation allows for contact-free determination of a substrate's electrical conductivity, even under paint or plastic coatings up to 500 µm thick. This method also marginalises the influence of surface roughness.



Measuring the electrical conductivity is an important element of quality assurance in the manufacture, maintenance and repair of aircraft



Sorting aluminium raw materials

Applications

The SMP350 can measure the electrical conductivity of any non-magnetisable metal. Furthermore, since the electrical conductivity provides data about other material properties, it is effective in a wide range of measuring applications and fields of use, including:

- Quality assurance and sorting of raw materials
- Authentication of coin alloys (e.g. specific conductivity of Euro coins)
- Determination of hardness and strength of heat-treated materials
- Inspection for heat damage, material fatigue and cracks
- Determination of the phosphorus content in copper
- Tracking precipitation processes, e.g. for Cu-Cr alloys
- Testing the homogeneity of alloys
- Scrap metal sorting

Hardware

The SIGMASCOPE® SMP350 is equipped with a Windows™ CE operating system and an intuitive graphical user interface that drives a high-resolution touchscreen operable with stylus or finger. The corresponding probes are suited for different measurement frequencies. For automatic compensation of temperature influences on the measurement, the ambient or specimen temperature can be taken directly with the integrated (or optional external) temperature sensor.



Quality assurance to avoid colour differences in anodised aluminium

Features

- Windows™ CE operating system with large touch-screen and displayable keyboard
- Individually adaptable user interface
- Very simple calibration via user prompts
- Simple management of measuring applications with user-definable file and folder structure
- Memory for several thousand measuring applications and several thousand readings
- Individual consideration of the electrical conductivity's temperature coefficient, applicable for each material
- Automatic measurement acquisition in free-running mode or with external start
- Graphical presentation of specification limits
- Extensive statistical evaluation of test series with date/time stamp as well as computation of C_p , C_{pk} and histogram presentation
- Manual temperature input
- Monitoring of temperature changes over time ($\Delta T/\Delta t$)
- Factory-provided master calibration with 8 standards at 20°C
- Acoustic signal for measurement acquisition and violation of specification limits
- Various languages available

Technical Data

- Measurements pursuant to standards ASTM E 1004 and DIN EN 2004-1
- Different measurement frequencies from 15 kHz up to 1 MHz depending on the probe
- Measurement range: 0.5 - 65 MS/m or 1 - 112 %IACS
- Measurement precision at ambient temperature: $\pm 0.5\%$ of reading
- Lift-off compensation to 500 μm
- Smallest diameter measurement area without noticeable influence on the reading: 13 mm
- Probe-internal or optional external temperature sensor
- USB communication and printer port

Calibration standards

High-precision measurements are required to determine the electrical conductivity. Because the eddy current method is a comparative measurement method, accurate standards are necessary to calibrate the measuring instrument. Certified standards are available for the entire conductivity range.



Certified standards for calibrating the SIGMASCOPE® SMP350, traceable to internationally-recognised calibration norms

Order Information

Product	Order no.
SIGMASCOPE® SMP350*	605-219
Measurement probe FS40	605-209
Measurement probe FS40HF	605-210
Measurement probe FS40LF	605-211
Optional accessories	
Temperature sensor TF100	603-237
Rechargeable battery set	604-144
Power unit	603-233

* Included in the shipment: Carrying case, power unit, batterie set, carrying strap and protective cover for the instrument, Cu reference standard

Product	Order no.	
Calibration standards**		
KAL-N SMP Al 2024/T3511	17,0 MS/m 29,3% IACS	600-373
KAL-N SMP Al 7175/T7351	22,0 MS/m 37,9% IACS	600-374
KAL-N SMP Al 99.5	34,2 MS/m 58,6% IACS	600-376
KAL-N SMP AlMgSi F32	28,0 MS/m 48,3% IACS	600-375
KAL-N SMP Bronze RG7	9,0 MS/m 15,5% IACS	600-380
KAL-N SMP Cu 58 Ms/m	58,0 MS/m 100% IACS	600-377
KAL-N SMP Manganin	2,3 MS/m 4,0% IACS	603-558
KAL-N SMP Brass	15,0 MS/m 25,9% IACS	600-381
KAL-N SMP Nickel Silver	5,0 MS/m 8,6% IACS	600-379
KAL-N SMP NORDIC GOLD	9,6 MS/m 16,5% IACS	602-603
KAL-N SMP Titanium LT31	0,6 MS/m 1,0% IACS	600-378

**Certificates for calibration standards have to be ordered seperately

Helmut Fischer GmbH
Institut für Elektronik und Messtechnik
 71069 Sindelfingen, **Germany**



Helmut Fischer AG and
Helmut Fischer Technologie AG
 CH-6331 Hünenberg, **Switzerland**



IfG-Institute for Scientific Instruments GmbH
 12489 Berlin, **Germany**

Fischer Instrumentation (GB) Ltd
 Lymington, Hampshire SO41 8JD, **England**



Fischer Technology, Inc.
 Windsor, CT 06095, **USA**



Helmut Fischer S. de R.L. de C.V.
 76230 Querétaro, QRO, **Mexico**

Fischer Instrumentation Electronique
 78180 Montigny le Bretonneux, **France**

Helmut Fischer S.R.L.
 20099 Sesto San Giovanni (Milano), **Italy**

Fischer Instruments, S.A.
 08018 Barcelona, **Spain**

Helmut Fischer Meettechniek B.V.
 5627 GB Eindhoven, **The Netherlands**

Fischer do Brasil
 04561-001 São Paulo, **Brazil**

Fischer Instruments K.K.
 Saitama-ken 340-0012, **Japan**

Nantong Fischer Instrumentation Ltd
 Shanghai 200333, **P.R. China**



Fischer Instrumentation (Far East) Ltd
 Kwai Chung, N.T., **Hong Kong**

Fischer Measurement Technologies (India) Pvt. Ltd
 Pune 411036, **India**

Fischer Instrumentation (S) Pte Ltd
 Singapore 658065, **Singapore**

Helmut Fischer Korea Co., Ltd
 Seoul City, **Republic of Korea**

Fischer Technology (M) SDN Bhd
 47301 Petaling Jaya, **Malaysia**

Helmut Fischer Thailand Co., Ltd
 Bangkok 10250, **Thailand**



www.helmut-fischer.com